

Gel List A (BioRad Type)

| Cat. No. | Buffer | 孔数 | 厚度/mm | Max. Vol/ul | 类型 | 浓度 |
|------------|--------------|----|-------|-------------|----|-------|
| RTG1010S08 | Tris-Glycine | 10 | 1.0 | 50 | 固定 | 8% |
| RTG1010S12 | Tris-Glycine | 10 | 1.0 | 50 | 固定 | 12% |
| RTG1010S16 | Tris-Glycine | 10 | 1.0 | 50 | 固定 | 16% |
| RTG1010S20 | Tris-Glycine | 10 | 1.0 | 50 | 固定 | 20% |
| RTG1010G12 | Tris-Glycine | 10 | 1.0 | 50 | 梯度 | 4-12% |
| RTG1010G16 | Tris-Glycine | 10 | 1.0 | 50 | 梯度 | 4-16% |
| RTG1010G20 | Tris-Glycine | 10 | 1.0 | 50 | 梯度 | 4-20% |
| RTG1510S12 | Tris-Glycine | 15 | 1.0 | 35 | 固定 | 12% |
| RTG1510S20 | Tris-Glycine | 15 | 1.0 | 35 | 固定 | 20% |
| RTG1510G12 | Tris-Glycine | 15 | 1.0 | 35 | 梯度 | 4-12% |
| RTG1510G20 | Tris-Glycine | 15 | 1.0 | 35 | 梯度 | 4-20% |
| RTG1015S12 | Tris-Glycine | 10 | 1.5 | 70 | 固定 | 12% |
| RTG1015S20 | Tris-Glycine | 10 | 1.5 | 70 | 固定 | 20% |
| RTG1015G12 | Tris-Glycine | 10 | 1.5 | 70 | 梯度 | 4-12% |
| RTG1015G20 | Tris-Glycine | 10 | 1.5 | 70 | 梯度 | 4-20% |
| RTG1515S12 | Tris-Glycine | 15 | 1.5 | 50 | 固定 | 12% |
| RTG1515S20 | Tris-Glycine | 15 | 1.5 | 50 | 固定 | 20% |
| RTG1515G12 | Tris-Glycine | 15 | 1.5 | 50 | 梯度 | 4-12% |
| RTG1515G20 | Tris-Glycine | 15 | 1.5 | 50 | 梯度 | 4-20% |

| Cat. No. | Buffer | 孔数 | 厚度/mm | Max. Vol/ul | 类型 | 浓度 |
|------------|----------|----|-------|-------------|----|-------|
| RBT1010S08 | Bis-Tris | 10 | 1.0 | 50 | 固定 | 8% |
| RBT1010S12 | Bis-Tris | 10 | 1.0 | 50 | 固定 | 12% |
| RBT1010S16 | Bis-Tris | 10 | 1.0 | 50 | 固定 | 16% |
| RBT1010S20 | Bis-Tris | 10 | 1.0 | 50 | 固定 | 20% |
| RBT1010G12 | Bis-Tris | 10 | 1.0 | 50 | 梯度 | 4-12% |
| RBT1010G16 | Bis-Tris | 10 | 1.0 | 50 | 梯度 | 4-16% |
| RBT1010G20 | Bis-Tris | 10 | 1.0 | 50 | 梯度 | 4-20% |
| RBT1510S12 | Bis-Tris | 15 | 1.0 | 35 | 固定 | 12% |
| RBT1510S20 | Bis-Tris | 15 | 1.0 | 35 | 固定 | 20% |
| RBT1510G12 | Bis-Tris | 15 | 1.0 | 35 | 梯度 | 4-12% |
| RBT1510G20 | Bis-Tris | 15 | 1.0 | 35 | 梯度 | 4-20% |
| RBT1015S12 | Bis-Tris | 10 | 1.5 | 70 | 固定 | 12% |
| RBT1015S20 | Bis-Tris | 10 | 1.5 | 70 | 固定 | 20% |
| RBT1015G12 | Bis-Tris | 10 | 1.5 | 70 | 梯度 | 4-12% |
| RBT1015G20 | Bis-Tris | 10 | 1.5 | 70 | 梯度 | 4-20% |
| RBT1515S12 | Bis-Tris | 15 | 1.5 | 50 | 固定 | 12% |
| RBT1515S20 | Bis-Tris | 15 | 1.5 | 50 | 固定 | 20% |
| RBT1515G12 | Bis-Tris | 15 | 1.5 | 50 | 梯度 | 4-12% |
| RBT1515G20 | Bis-Tris | 15 | 1.5 | 50 | 梯度 | 4-20% |